




**CONDUIT CLAMPS**

**Right Angle Clamp Galvanized Malleable Iron**  
N/A

**B85**



Catalog #: 2362RC

**APPLICATIONS**

To secure Rigid/IMC or EMT conduit across, parallel, or perpendicular to channel, beam, and angle supports  
N/A

**PRODUCT FEATURES**

- Three styles meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications

**CULUS**

UL Listed E195968

**GENERAL PRODUCT INFORMATION**

Trade Size: 3 in.

**DRAWING DIMENSIONS**

- Dimension A: 3-1/2 in.
- Dimension B: 3-7/8 in.
- Dimension C: 5-3/8 in.
- Dimension D: 2-5/8 in.
- Dimension E: 5-1/8 in.

**PACKAGING**

- Package Type: Carton
- Ship Carton Qty.: 5
- Product UPC-A Labeled: No
- Weight (Lbs. Per/C): 126.40
- Ship Carton Length (in.): 8.00
- Ship Carton Width (in.): 6.00
- Ship Carton Height (in.): 4.00
- Ctn Weight (Lbs.): 6.32
- UPC Number: 050169986271
- I2of5: 50050169986276