



\* Representative image

# 35 kV Class Large Interface Elbow Arrester (29 kV MCOV)

by Hubbell Power Systems  
Catalog ID: 236ELA36

ELBOW ARRESTER, 35KV 29 MCOV, Mates with IEEE Std. 386, Interface 9

## Product Details

### General

Grounding Style	36 in Line Lead
Type	Underground Arresters
UPC	096359695363

### Electrical Ratings

Duty Cycle	36 kV
MCOV	29 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 117.4 kV @ 1.5 kA</li> <li>• 100.5 kV @ 3 kA</li> <li>• 107.2 kV @ 5 kA</li> <li>• 120.7 kV @ 10 kA</li> <li>• 139.4 kV @ 20 kA</li> <li>• 174.3 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	84.5 kV
kV Class	35 kV

### Logistics

Pallet Quantity	64 EA
Standard Package	1

For further technical assistance, please contact us

**Domestic Customer Service**  
 Hubbell Power Systems  
 210 N. Allen Centralia, MO 65240 USA  
 Phone: (573) 682-5521  
 Fax: (573) 682-8475  
 Email: hpscsc@hubbell.com

**International Customer Service**  
 Phone: +1-573-682-5521  
 Fax: +1-573-682-8516  
 Email: hpsintlcs@hubbell.com