




## 4 IN. SQUARE WELDED BOXES - 1-1/2 IN. DEEP WITH ARMORED CABLE / METAL CLAD / FLEX CLAMPS

4 in. Square Bracketed Boxes, 2-1/8 in. Deep - Welded with Armored Cable/Metal Clad/Flex Clamps  
BOX-LOC®, MS, Flush, Provided with Far-side support (part #978)

A18



Catalog #: 243

### APPLICATIONS

RACO® Boxes are installed in walls or ceilings for lighting fixtures, switches or receptacles  
Square boxes are used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices

### PRODUCT FEATURES

Reference the Box Selection section in the front of this catalog for complete description of bracket types and features  
Combination screw heads provide for faster installation  
TKO® Knockouts offer greater flexibility with RACO patented combination 1/2" and 3/4" knockout  
BOX-LOC® (MS) Bracket Box is a snap to install. Place the bracket on the open side of the stud first. Slots in the bracket engage the lip of the stud and actually crimp it as you press the bracket on the stud, quickly locking it in place  
N/A

### UL LISTED

File E 195978

### COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com  
600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

### FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

### GENERAL PRODUCT INFORMATION

Wiring System: Armored Cable/Metal Clad/MCI-A/Flex

### CONFIGURATION

Cable Priouts: 4  
Bracket Type: BOX-LOC®, for Metal Studs  
Bracket Setback: Flush  
Drawn or Welded: Welded  
Raised Ground: No  
Side Knockout(s): (2) 1/2 in. & (1) TKO®  
Bottom Knockouts(s): (1) 1/2 in.

### DRAWING DIMENSIONS

Dimension A: 2-1/8 in.  
Dimension B: 4-5/8 in.  
Dimension C: 5-1/2 in.

### PRODUCT MEASUREMENTS

Depth: 2-1/8 in.  
Cubic Inches (cm3): 30.3 (496.5)  
Wt. Ea. (Lbs.): 1.068  
Product Length (in.): 2.19  
Product Width (in.): 4.63  
Product Height (in.): 5.50

### PACKAGING

Minimum Pack Qty.: 25  
Std. Pkg.: 25  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 106.80  
Ship Carton Length (in.): 20.25  
Ship Carton Width (in.): 8.50  
Ship Carton Height (in.): 10.25  
Ctn Weight (Lbs.): 26.70  
Pallet Qty: 1250  
UPC Number: 050169002438  
I2of5: 50050169002433

