



**Commercial, Industrial  
and Residential Electrical Products**

## 4 In. Square Box, Welded with (2) STAB-iT® Connectors on Top, 2-1/8 In. Deep, 600V, 8 In. #12 Solid Copper Pigtail, USB, M Bracket

Catalog #:  
244MS



### FEATURE BENEFIT

- Install MC into the box in one third the time using STAB-iT boxes with our unique built-in cable clamps
- Holds up to 4 cables

### PRODUCT FEATURES

- Welded steel construction with "UBS" support with preset bend points to work with wall thickness 2-1/2 to 6 in., "M" steel brackets on both sides of the box, two STAB-IT® connectors
- 4 in. square x 2-1/8 in. deep
- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- TKO® Knockouts allow for design and installation flexibility
- Supplied with seven 1/2 in. and four 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Includes 8 in. #12 solid copper ground screw
- Acceptable for use in 2-hour fire rated walls
- Built-in cable clamps are releasable, reusable.

### APPLICATIONS

- For any job using flexible armored cable
- Ideal for Pre-Fab

### CERTIFICATIONS



### PRODUCT SPECIFICATIONS

UPC Number:	050169992449
Ea Length/Depth (in.):	2.64
Ea Width (in.):	5.86
Ea Height (in.):	4.14
Wt. Ea. (Lbs.):	1.212
Package Type:	Loose
Product UPC-A Labeled:	No

### PACKAGING

Case I2of5:	50050169992444
Standard Carton Qty:	25
Min Order Qty:	25



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at [www.ul.com](http://www.ul.com)

Revision 1, August 2019



**COMMERCIAL  
CONSTRUCTION**  
A Division of Hubbell Incorporated (Delaware)

RACO  
3902 W. Sample St.  
South Bend, IN 46619  
574-234-7151  
[www.hubbell.com/raco/en](http://www.hubbell.com/raco/en)

