



*Commercial, Industrial
and Residential Electrical Products*

3-3/4 In. Square Box, Large capacity, Welded, 3-1/2 In. Deep, Fourteen 1/2 & 3/4 In. Concentric KO's, FM Bracket

Catalog #:
255



FEATURE BENEFIT

3-3/4 In. boxes provide extra space around the box when used with 4 In. covers

PRODUCT FEATURES

- Welded steel construction with "FM" bracket that mounts on flat side of stud
- 3-3/4 In. square x 3-1/2 In. deep
- 3-3/4 In. opening in walls allows for margin of error when using a 4 In. square cover
- Accepts 4 In. square covers and mud rings
- Large capacity design accommodates oversized devices
- Supplied with fourteen 1/2-3/4 In. concentric knockouts and one 1/2 In. KO
- 40.5 Cu. In. capacity
- Acceptable for use in 2-hour fire rated walls

APPLICATIONS

- RACO® Large capacity boxes are used for audio, video, data and power applications providing ample space for Cat 6A and fiber optic cable bends

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169002551
Ea Length/Depth (in.):	3.50
Ea Width (in.):	4.125
Ea Height (in.):	7.625
Wt. Ea. (Lbs.):	1.426
Package Type:	Loose
Product UPC-A Labeled:	No

PACKAGING

Case I2of5:	50050169002556
Standard Carton Qty:	10
Min Order Qty:	10



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

600V

Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 2, April 2020



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

