



*Commercial, Industrial
and Residential Electrical Products*

3-3/4 In. Square Box, Large capacity, Welded, 3-1/2 In. Deep,
Sixteen 1/2 & 3/4 In. Concentric KO's and One 1/2 In. KO

Catalog #:
256



FEATURE BENEFIT

3-3/4 In. boxes provide extra space around the box when used with 4 In. covers

PRODUCT FEATURES

- Welded steel construction
- 3-3/4 in. square x 3-1/2 in. deep
- 3-3/4 in. opening in wall allows for margin of error when using a 4 in. square cover
- Accepts all 4 in. square covers and mudrings
- Large capacity design accommodates oversized devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with sixteen 1/2-3/4 In. Concentric KO's and one 1/2 In. KO
- 40.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

APPLICATIONS

- RACO® Large capacity boxes are used for audio, video, data and power applications providing ample space for Cat 6A and fiber optic cable bends

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169002568
Ea Length/Depth (in.):	3.50
Ea Width (in.):	3.75
Ea Height (in.):	3.75
Wt. Ea. (Lbs.):	1.204
Package Type:	Loose
Product UPC-A Labeled:	No



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

PACKAGING

Case I2of5:	50050169002563
Standard Carton Qty:	25
Min Order Qty:	25



Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 2, April 2020



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

