




4-11/16 IN. SQUARE WELDED BOXES 2-1/8 IN. WITH CONDUIT KO'S

4-11/16 in. Square Bracketed Boxes, 2-1/8 in. Deep - Welded with Conduit KO's
600V, Raised Ground, 8 in. #12 Solid Copper Pigtail, UBS

A26



Catalog #: 257F

APPLICATIONS

RACO® 4-11/16" Boxes are used for a wide variety of industrial applications where larger sized conductors or wiring devices are needed and more volume is required
N/A

PRODUCT FEATURES

Combination screw heads provide for faster installation
TKO knockouts allow for design and installation flexibility
UBS Support - Welded to box, preset bend points to work with wall thickness 2-1/2" to 6"

UL LISTED

File E195978

COMPLIANCES

600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

Bracket Type: No Bracket
Drawn or Welded: Welded
Raised Ground: Yes
Side Knockout(s): (12) TKO®
Bottom Knockouts(s): (1) 1/2 in. & (3) TKO®

DRAWING DIMENSIONS

Dimension A: 2-1/8 in.

PRODUCT MEASUREMENTS

Depth: 2-1/8 in.
Cubic Inches (cm3): 42.0 (688.2)
Wt. Ea. (Lbs.): 1.150
Product Length (in.): 2.19
Product Width (in.): 4.69
Product Height (in.): 4.69

PACKAGING

Minimum Pack Qty.: 20
Std. Pkg.: 20
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 115.00
Ship Carton Length (in.): 18.13
Ship Carton Width (in.): 7.88
Ship Carton Height (in.): 11.63
Ctn Weight (Lbs.): 21.92
Pallet Qty: 1080
UPC Number: 050169500088
I2of5: 50050169500083