

4-11/16 In. Square Box, 2-1/8 In. Deep - Welded w/Conduit KO's 600V, Raised Ground, 10 In. #12 Stranded Copper Pigtail

Catalog #:
258SM



FEATURE BENEFIT

Larger 4-11/16 In. box with the strength of welded steel offers connection flexibility with a variety of knockouts

PRODUCT FEATURES

- Combination screw heads provide faster installation
- Three TKO knockouts allow for design and installation flexibility
- One 1/2 In. knockout
- Eight 1 In. knockouts

APPLICATIONS

- 4-11/16 In. box is used for a wide variety of industrial applications where larger sized conductors or wiring devices are needed and more volume is required

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169982587
Ea Length/Depth (in.):	2.188
Ea Width (in.):	4.688
Ea Height (in.):	4.688
Wt. Ea. (Lbs.):	1.157
Package Type:	Loose
Package Contents:	1
Product UPC-A Labeled:	Yes

SHIPPING

I2of5:	50050169982582
Standard Carton Qty:	25
Min Order Qty:	25
Ship Carton Length (in.):	21.50
Ship Carton Width (in.):	10.10
Ship Carton Height (in.):	7.50
Ship Carton Weight (Lbs.):	28.925
Pallet Qty:	1500



600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

Revision 1, September 2018

