




LARGE CAPACITY BOXES

4-11/16 in. Larger Capacity Steel Wall Boxes, 3-1/4" Deep - Welded with Conduit KO's
Raised Ground, H Bracket, Far-Side Box Support

A32



Catalog #: 260H

APPLICATIONS

RACO® Large capacity boxes are used for audio, video, data and power applications providing ample space for Cat 6A and fiber optic cable bends

PRODUCT FEATURES

- 4-11/16" Square, 3-1/4" Deep Box
- Accepts Standard 4-11/16" Covers
- "H" Bracket for mounting to metal or wood studs
- Far-Side box support for stud size up to 6 inches
- Includes Knockouts - 1/2" through 2"
- Three Pre-installed ground screws

UL LISTED

File E195978

COMPLIANCES

They are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com
MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System:	Conduit
Color:	Gray

CONFIGURATION

Bracket Type:	"H" Bracket
Bracket Setback:	---
Drawn or Welded:	Welded
Raised Ground:	Yes
Gangs:	2
Side Knockout(s):	(2) 1/2-3/4 in., (2) 3/4-1 in., (2) 1 - 1-1/4 in., (2) 1-2 in., 1/2 in. & 3/4 in. TKO
Bottom Knockouts(s):	(2) 1/2 in., (2) 3/4-1 in.

DRAWING DIMENSIONS

Dimension A: 3-1/4 in.

PRODUCT MEASUREMENTS

Depth:	3-1/4 in.
Cubic Inches (cm3):	66.7 (1093)
Wt. Ea. (Lbs.):	1.651
Product Length (in.):	4.690
Product Width (in.):	4.690
Product Height (in.):	3.250

PACKAGING

Package Type:	Boxed
Minimum Pack Qty.:	10
Std. Pkg.:	10
Ship Carton Qty.:	10
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	165.100
Ship Carton Length (in.):	13.190
Ship Carton Width (in.):	7.310
Ship Carton Height (in.):	9.880
Ctn Weight (Lbs.):	16.510
Pallet Qty:	720
UPC Number:	050169500507
I2of5:	50050169500502

