




LARGE CAPACITY BOXES

4-11/16 in. Large Capacity Steel Wall Boxes, 3-1/4 in. Deep - Welded with Conduit KO's Raised Ground

A32



Catalog #: 263

APPLICATIONS

RACO® Large capacity boxes are used for audio, video, data and power applications providing ample space for Cat 6A and fiber optic cable bends

PRODUCT FEATURES

- Large capacity design measures 4-11/16" H x 7-3/4" W x 3-1/4" D
- Accepts standard 4" square device and flat covers or 792, 793, 794 3-gang device covers
- Built-in tabs for spanner bars
- Includes 1/2" thru 2" knockouts
- Accepts 981 voltage partition (UL Listed)
- Ground screw provided

UL LISTED

File E195978

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO MSDS for Steel Boxes & Covers.pdf

US PATENTS

Patent Pending

GENERAL PRODUCT INFORMATION

Wiring System: Conduit
 Color: Gray

CONFIGURATION

Bracket Type: No Bracket
 Drawn or Welded: Welded
 Raised Ground: Yes
 Gangs: 2 or 3
 Side Knockout(s): (6) 1/2-3/4 in., (2) 3/4-1 in., (2) 1 - 1-1/4 in., (2) 1-2 in., 1/2 in & 3/4 in. TKO
 Bottom Knockouts(s): (2) 1/2-3/4 in., (2) 3/4-1 in., (2) 1 - 1-1/4 in.

DRAWING DIMENSIONS

Dimension A: 3-1/4 in.
 Dimension B: 7-3/4 in.
 Dimension C: 4-11/16 in.

PRODUCT MEASUREMENTS

Depth: 3-1/4 in.
 Cubic Inches (cm3): 113.3 (1856.6)
 Wt. Ea. (Lbs.): 2.850
 Product Length (in.): 9.69
 Product Width (in.): 3.50
 Product Height (in.): 5.50

PACKAGING

Minimum Pack Qty.: 6
 Std. Pkg.: 6
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 285.00
 Ship Carton Length (in.): 17.13
 Ship Carton Width (in.): 7.50
 Ship Carton Height (in.): 10.19
 Ctn Weight (Lbs.): 17.90
 Pallet Qty: 288
 UPC Number: 050169002636
 I2of5: 50050169002631