




4-11/16 IN. SQUARE WELDED BOXES 2-1/8 IN. WITH CONDUIT KO'S

4-11/16 in. Square Bracketed Boxes, 2-1/8 in. Deep - Welded with Conduit KO's
600V, BOX-LOC®, MS, Flush, Provided with Far-side support (part #978)

A26



Catalog #: 266

APPLICATIONS

RACO® 4-11/16" Boxes are used for a wide variety of industrial applications where larger sized conductors or wiring devices are needed and more volume is required
N/A

PRODUCT FEATURES

Reference the Box Selection section in the front of this catalog for complete description of bracket types and features
Combination screw heads provide for faster installation
TKO knockouts allow for design and installation flexibility
BOX-LOC® (MS) Bracket Box is a snap to install. Place the bracket on the open side of the stud first. Slots in the bracket engage the lip of the stud and actually crimp it as you press the bracket on the stud, quickly locking it in place

UL LISTED

File E195978

COMPLIANCES

600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

BOX-LOC®, for Metal Studs
Bracket Type: Flush
Bracket Setback: Welded
Drawn or Welded: Yes
Raised Ground: (9) TKO®
Side Knockout(s): (1) 1/2 in. & (3) TKO®
Bottom Knockouts(s): 2-1/8 in.

DRAWING DIMENSIONS

4-5/8 in.
6-3/16 in.

PRODUCT MEASUREMENTS

Depth: 2-1/8 in.
Cubic Inches (cm3): 42.0 (688.2)
Wt. Ea. (Lbs.): 1.207
Product Length (in.): 2.19
Product Width (in.): 4.69
Product Height (in.): 6.19

PACKAGING

Minimum Pack Qty.: 25
Std. Pkg.: 25
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 120.70
Ship Carton Length (in.): 20.25
Ship Carton Width (in.): 9.50
Ship Carton Height (in.): 12.25
Ctn Weight (Lbs.): 30.18
Pallet Qty: 1000
UPC Number: 050169002667
I2of5: 50050169002662