


**EMT HANDY ELLS - DIE CAST ZINC**90 Degree Handy Ells Male-Female Die cast Zinc
N/A**B13**

Catalog #: 2763

APPLICATIONSFor use in dry locations to bond EMT conduit to a box or enclosure
Use handy ells when bending conduit is not practical**PRODUCT FEATURES**Cover and screws included
Rugged metallic construction provides mechanical protection for the raceway
N/A**UL LISTED**

File E195969

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.

DRAWING DIMENSIONS

Dimension A:	1-13/16 in.
Dimension B:	15/16 in.
Dimension C:	1-3/16 in.
Dimension D:	8-32 x 1/4 in.
Dimension E:	10-32 x 5/16 in.
Dimension F:	1-13/32 in.
Dimension G:	3/4 in. - 14 NPSM

PACKAGING

Package Type:	Carton
Std. Pkg.:	5
Ship Carton Qty.:	50
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	45.00
Ship Carton Length (in.):	19.00
Ship Carton Width (in.):	10.63
Ship Carton Height (in.):	4.13
Ctn Weight (Lbs.):	17.50
UPC Number:	050169027639
I2of5:	50050169027634