




CEILING PANS

3-1/2 in. Round Ceiling Pan - Drawn with Nonmetallic Sheathed Cable Clamps
3/4 in. Depth

A36.1



Catalog #: 287

APPLICATIONS

RACO® Ceiling Pans are used in the installation of ceiling or wall lighting fixtures

PRODUCT FEATURES

Combination screw heads provide for faster installation

UL LISTED

File E195978

US PATENTS

7,148,420; 4,892,211

OTHER PATENTS

Canada 1,324,360; Mexico 166.125

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: No
Fixture (Static) Lbs.: 50

CONFIGURATION

Cable Priouts: 4
Drawn or Welded: Drawn
Raised Ground: No
Side Knockout(s): ---
Bottom Knockouts(s): (1) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 11/16 in.
Dimension B: 3-3/8 in.

PRODUCT MEASUREMENTS

Depth: 3/4 in.
Cubic Inches (cm3): 5.0 (81.9)
Wt. Ea. (Lbs.): 0.340
Product Length (in.): 0.75
Product Width (in.): 3.38
Product Height (in.): 3.38

PACKAGING

Minimum Pack Qty.: 50
Std. Pkg.: 50
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 34.00
Ship Carton Length (in.): 12.88
Ship Carton Width (in.): 5.63
Ship Carton Height (in.): 8.75
Ctn Weight (Lbs.): 17.00
Pallet Qty: 6300
UPC Number: 050169002872
I2of5: 50050169002877