




EMT COMPRESSION COUPLINGS

Compression Couplings, Steel

B06



Catalog #: 2922-8

APPLICATIONS

For use in dry locations to couple two ends of EMT conduit
RACO Compression couplings are suitable for applications above 600V

PRODUCT FEATURES

RACO Steel compression couplings provide concrete-tight connections
All steel construction ensures mechanical protection for the raceway
All components are zinc electroplated for corrosion protection
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation.

CULUS

Standard 514B, UL Listed E195970, C22.2 No. 18

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings,January_2015.pdf

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2.00 in.
Dimension B: 1.16 in.

PACKAGING

Package Type: Carton
Std. Pkg.: 1
Ship Carton Qty.: 25
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 13.80
Ship Carton Length (in.): 6.25
Ship Carton Width (in.): 4.50
Ship Carton Height (in.): 4.25
Ctn Weight (Lbs.): 3.45
UPC Number: 050169292280
I2of5: 50050169292285