


**EMT COMPRESSION COUPLINGS**

Compression Couplings, Steel

B06

Catalog #: 2922US

APPLICATIONS

For use in dry locations to couple two ends of EMT conduit
 RACO Compression couplings are suitable for applications above 600V

PRODUCT FEATURES

RACO Steel compression couplings provide concrete-tight connections
 All steel construction ensures mechanical protection for the raceway
 All components are zinc electroplated for corrosion protection
 UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation.

CULUS

Standard 514B, UL Listed E195970, C22.2 No. 18

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings,January_2015.pdf

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2.00 in.
 Dimension B: 1.16 in.

PACKAGING

Package Type: Carton
 Std. Pkg.: 50
 Ship Carton Qty.: 250
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 8.00
 Ship Carton Length (in.): 19.88
 Ship Carton Width (in.): 10.75
 Ship Carton Height (in.): 9.50
 Ctn Weight (Lbs.): 63.50
 UPC Number: 050169570425
 I2of5: 50050169570420