


# 2AB-750

by CMC  
Catalog ID: 2AB-750



Dual Rated Solderless Connector, wire range 750 AWG - 1/0 AWG. TYPE: 2AB/2AB2. The unique ridges formed on the bottom of the contact surface are redesigned to provide contact points for an electrically secure joint of the lowest resistance for current flow. The screws used to clamp the conductors are designed to extend beyond the barrel sides of the conductor to allow a better, more secure compression of the conductor. This design spreads the conductor strands to help dissipate heat, and improve its pull-out safety features and capabilities. The design of the wire way provides optimum transfer of current creating a straight line flow through the connector for the least possible path of electrical resistance. A positive wire stop is also provided. 90° C Rated (486B Listed). UL listed and CSA certified.

## Product Details

### General

Material	Aluminum
Type	Bolted Lugs & Terminals
UPC	192663135202

### Dimensions

Dimensions	3.25 in x 3.5 in x 1.81 in
Height	1.81 in
Length	3.25 in
Thickness	0.44 in
Width	3.5 in

### Conductor Related

Conductor - Copper Str Size Range	750 Kcmil-1/0 AWG
-----------------------------------	-------------------