



Vertical Pin Standoff Bracket, 36" Two-Phase

by CHANCE Utility
Catalog ID: 2SBH36VV1

36" Heavy Duty Fiberglass Two-Phase Vertical Pin Standoff Bracket with
1" Plastisol Coated Threads



* Representative image

Product Details

General

Description - End Fitting	Vertical Pin
Material - Threads	1" Plastisol Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	2000 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2550 lb
UPC	096359069065

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	36 in
Length	36.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	20.8 lb

Logistics

Pallet Quantity	20 EA
Standard Package	4

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com