


**AC CABLE 90 DEGREE SQUEEZE TYPE**
**90° Squeeze Connectors, Insulated Throat Malleable Iron**  
 N/A

**B69**


Catalog #: 3201

**APPLICATIONS**

- For use in dry locations to bond flexible metal conduit to a box or enclosure
- N/A
- For use in dry locations to bond armored cable to a box or enclosure

**PRODUCT FEATURES**

- All malleable iron construction insures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

**CULUS**

UL Listed E195969

**GENERAL PRODUCT INFORMATION**

Sub Class:	Insulated
Trade Size:	3/8 in.

**DRAWING DIMENSIONS**

Dimension A:	2-1/64 in.
Dimension B:	23/64 in.
Thread Spec. B:	1/2 in. - 14 NPS
Dimension C:	.570 in.
Dimension D:	.390-.630 in.
Dimension E:	1-3/8 in.

**PACKAGING**

Package Type:	Carton
Ship Carton Qty.:	50
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	8.80
Ship Carton Length (in.):	10.00
Ship Carton Width (in.):	5.25
Ship Carton Height (in.):	4.31
Ctn Weight (Lbs.):	4.40
UPC Number:	050169032015
I2of5:	50050169032010