


**FLEXIBLE METAL 90 DEGREE SQUEEZE CONNECTORS**90° Squeeze Connectors Malleable Iron
N/A**B63**

Catalog #: 3205

APPLICATIONSFor use in dry locations to bond flexible metal conduit to a box or enclosure
N/A**PRODUCT FEATURES**All malleable iron construction insures mechanical protection for the raceway
Electro zinc plated for added corrosion protection
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation**CULUS**

UL Listed E195969

GENERAL PRODUCT INFORMATIONSub Class: Insulated
Trade Size: 1-1/4 in.**DRAWING DIMENSIONS**Dimension A: 4-13/64 in.
Dimension B: 43/64 in.
Thread Spec. B: 1-1/4 in. - 11-1/2 NPS
Dimension C: 1.210 in.
Dimension D: 1.535 in. MAX
Dimension E: 2-55/64 in.**PACKAGING**Package Type: Carton
Ship Carton Qty.: 10
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 120.80
Ship Carton Length (in.): 8.25
Ship Carton Width (in.): 6.00
Ship Carton Height (in.): 5.50
Ctn Weight (Lbs.): 12.08
UPC Number: 050169032053
I2of5: 50050169032058