


**FLEXIBLE METAL 90 DEGREE SQUEEZE CONNECTORS**90° Squeeze Connectors Malleable Iron  
N/A**B63**

Catalog #: 3206

**APPLICATIONS**For use in dry locations to bond flexible metal conduit to a box or enclosure  
N/A**PRODUCT FEATURES**All malleable iron construction insures mechanical protection for the raceway  
Electro zinc plated for added corrosion protection  
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation**CULUS**

UL Listed E195969

**GENERAL PRODUCT INFORMATION**Sub Class: Insulated  
Trade Size: 1-1/2 in.**DRAWING DIMENSIONS**Dimension A: 4-57/64 in.  
Dimension B: 19/32 in.  
Thread Spec. B: 1-1/2 in. - 11-1/2 NPS  
Dimension C: 1.450 in.  
Dimension D: 1.890 in. MAX  
Dimension E: 3-3/32 in.**PACKAGING**Package Type: Carton  
Ship Carton Qty.: 5  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 150.70  
Ship Carton Length (in.): 8.25  
Ship Carton Width (in.): 8.25  
Ship Carton Height (in.): 6.00  
Ctn Weight (Lbs.): 7.54  
UPC Number: 050169032060  
I2of5: 50050169032065