




**FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS**

**Straight Squeeze Connectors, Insulated Malleable Iron**  
N/A

**B61**



Catalog #: 3303-8

**APPLICATIONS**

For use in dry locations to bond flexible metal conduit to a box or enclosure  
N/A

**PRODUCT FEATURES**

All malleable iron construction insures mechanical protection for the raceway  
Electro zinc plated for added corrosion protection  
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

**CULUS**

UL Listed E195969

**GENERAL PRODUCT INFORMATION**

Trade Size: 3/4 in.

**DRAWING DIMENSIONS**

Dimension A: 1-15/32 in.  
Dimension B: 31/64 in.  
Thread Spec. B: 3/4 in. - 14 NPS  
Dimension C: .763 in.  
Dimension D: 1.043 - 1.122  
Dimension E: 1-15/16 in.

**PACKAGING**

Package Type: Carton  
Std. Pkg.: 1  
Ship Carton Qty.: 20  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 18.10  
Ship Carton Length (in.): 8.75  
Ship Carton Width (in.): 5.00  
Ship Carton Height (in.): 4.00  
Ctn Weight (Lbs.): 3.62  
UPC Number: 050169330388  
I2of5: 50050169330383