


**MC CABLE DOUBLE BITE SADDLE CONNECTORS**Straight Double Bite Saddle Connectors Steel  
N/A**B74**

Catalog #: 3303DB

**APPLICATIONS**

Use 3/8 in. to 1 in. RACO Double Bite Saddle connectors in dry locations to connect flexible metal conduit, MCI, MCI-A, and AC cable to a box or enclosure  
 Use 1-1/4 in. to 4 in. in dry locations to connect flexible metal conduit to a box or enclosure

**PRODUCT FEATURES**

Straight connectors have all steel construction that ensures mechanical protection for raceways  
 Straight connectors are available in 3/8 in. to 4 in. trade sizes  
 90 degree connectors have malleable iron and steel construction for added strength  
 90 degree connectors are available in 3/8 in. to 1 in. trade sizes  
 Dual saddle clamp ensures proper conduit and cable connection for raceway  
 Zinc plated for corrosion protection  
 Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips, or Robertson head screwdriver  
 Insulated throats on all Double Bite connectors provide maximum wire protection  
 N/A

**UL LISTED**

Standard 514B, File E195978  
 Standard 514B, File E195979

**NEMA**

NEMA FB-13  
 NEMA FB-14

**GENERAL PRODUCT INFORMATION**

Trade Size: 3/4 in.

**DRAWING DIMENSIONS**

Dimension A: 1-3/8 in.  
 Dimension B: 1-7/16 in.  
 Dimension C: 7/16 in.

**PACKAGING**

Package Type: Carton  
 Ship Carton Qty.: 10  
 Product UPC-A Labeled: No  
 Weight (Lbs. Per/C): 17.20  
 Ship Carton Length (in.): 6.30  
 Ship Carton Width (in.): 5.80  
 Ship Carton Height (in.): 3.00  
 Ctn Weight (Lbs.): 1.72  
 UPC Number: 050169533031  
 I2of5: 50050169533036