




FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS

**Straight Squeeze Connectors, Insulated Malleable Iron
N/A**

B61



Catalog #: 3314

APPLICATIONS

For use in dry locations to bond flexible metal conduit to a box or enclosure
N/A

PRODUCT FEATURES

All malleable iron construction insures mechanical protection for the raceway
Electro zinc plated for added corrosion protection
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

CULUS

UL Listed E195969

GENERAL PRODUCT INFORMATION

Trade Size: 3-1/2 in.

DRAWING DIMENSIONS

Dimension A: 5-1/64 in.
Dimension B: 1-21/64 in.
Thread Spec. B: 3-1/2 in. - 8 NPS
Dimension C: 3.425 in.
Dimension D: 3.150 MAX
Dimension E: 6-5/8 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 1
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 446.40
Ship Carton Length (in.): 7.30
Ship Carton Width (in.): 5.60
Ship Carton Height (in.): 5.70
Ctn Weight (Lbs.): 4.46
UPC Number: 050169033142
I2of5: 50050169033147