


**FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS**Straight Squeeze Connectors, Insulated Malleable Iron  
N/A**B61**

Catalog #: 3316

**APPLICATIONS**For use in dry locations to bond flexible metal conduit to a box or enclosure  
N/A**PRODUCT FEATURES**All malleable iron construction insures mechanical protection for the raceway  
Electro zinc plated for added corrosion protection  
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation**CULUS**

UL Listed E195969

**GENERAL PRODUCT INFORMATION**

Trade Size: 4 in.

**DRAWING DIMENSIONS**Dimension A: 5-23/64 in.  
Dimension B: 1-39/64 in.  
Thread Spec. B: 4 in. - 8 NPS  
Dimension C: 3.915 in.  
Dimension D: 3.500 MAX  
Dimension E: 7-15/64 in.**PACKAGING**Package Type: Carton  
Ship Carton Qty.: 1  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 669.60  
Ship Carton Length (in.): 7.40  
Ship Carton Width (in.): 6.70  
Ship Carton Height (in.): 6.40  
Ctn Weight (Lbs.): 6.70  
UPC Number: 050169033166  
I2of5: 50050169033161