


**STRAIGHT CONDUIT AND CORD CONNECTORS - STEEL/MALLEABLE IRON**Straight Connectors Steel/Malleable Iron  
N/A

B47



Catalog #: 3403-8

**APPLICATIONS**

For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit  
Use to positively bond the conduit to a box or enclosure

**PRODUCT FEATURES**

RACO liquidtight connectors are suitable for use in Class I, Div. 2, Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations  
Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts  
All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service  
Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening  
Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground  
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation  
All steel/iron components are zinc electro plated for added corrosion protection  
3/8 in. to 1 in. Steel bodies, 1-1/4 in. to 4 in. Malleable iron bodies  
3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts  
N/A

**UL LISTED**

Standard 514B, UL Listed E195969

**CSA**

C22.2 No. 18

**GENERAL PRODUCT INFORMATION**

Sub Class: Uninsulated  
Trade Size: 3/4 in.

**DRAWING DIMENSIONS**

Dimension A: 1-13/32 in.  
Dimension B: 9/16 in.  
Thread Spec. B: 3/4 in. - 14 NPT

**PACKAGING**

Package Type: Carton  
Std. Pkg.: 1  
Ship Carton Qty.: 10  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 24.90  
Ship Carton Length (in.): 6.13  
Ship Carton Width (in.): 3.13  
Ship Carton Height (in.): 6.13  
Ctn Weight (Lbs.): 2.49  
UPC Number: 050169340387  
I2of5: 50050169340382