



STRAIGHT CORD CONNECTORS - DIE CAST ZINC

Straight Connectors Die Cast Zinc
N/A

B49



Catalog #: 3403DC

APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
Use to positively bond the conduit to a box or enclosure

PRODUCT FEATURES

Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service
Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
N/A

CULUS

Conduit Fittings 3HNN

GENERAL PRODUCT INFORMATION

Sub Class: Uninsulated
Trade Size: 3/4 in.

DRAWING DIMENSIONS

Dimension A: -
Thread Spec. A: -
Dimension B: -
Thread Spec. B: -
Dimension C: -
Thread Spec. C: -
Dimension C A/C: -
Dimension C A/F: -
Dimension D: -
Thread Spec. D: -
Dimension E: -
Thread Spec. E: -
Dimension F: -

PACKAGING

Package Type: Carton
Std. Pkg.: 25
Ship Carton Qty.: 100
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 17.60
Ship Carton Length (in.): 17.32
Ship Carton Width (in.): 6.30
Ship Carton Height (in.): 6.50
Ctn Weight (Lbs.): 17.64
UPC Number: 050169980064
I2of5: 50050169980069