


**90 DEGREE CONDUIT AND CORD CONNECTORS - STEEL/MALLEABLE IRON****90 Degree Connectors Steel/Malleable Iron**
N/A**B48**

Catalog #: 3422-8

APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
 Use to positively bond the conduit to a box or enclosure

PRODUCT FEATURES

RACO liquidtight connectors are suitable for use in Class I, Div. 2, Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations
 Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
 All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service
 Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
 Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
 UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
 All steel/iron components are zinc electro plated for added corrosion protection
 3/8 in. to 4 in. Malleable iron bodies
 3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts
 N/A

UL LISTED

Standard 514B, UL Listed E195969

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Sub Class: Uninsulated
 Trade Size: 1/2 in.

DRAWING DIMENSIONS

Dimension A: 1-11/64 in.
 Dimension B: 9/16 in.
 Thread Spec. B: 1/2 in. - 14 NPT
 Dimension C: 1-13/32 in.
 Dimension D: 1-5/8 in.

PACKAGING

Package Type: Carton
 Std. Pkg.: 1
 Ship Carton Qty.: 15
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 27.30
 Ship Carton Length (in.): 6.13
 Ship Carton Width (in.): 3.13
 Ship Carton Height (in.): 6.13
 Ctn Weight (Lbs.): 4.09
 UPC Number: 050169342282
 I2of5: 50050169342287