


**90 DEGREE CONDUIT AND CORD CONNECTORS - STEEL/MALLEABLE IRON****90 Degree Connectors Steel/Malleable Iron**  
N/A**B48**

Catalog #: 3542-8

**APPLICATIONS**For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit  
Use to positively bond the conduit to a box or enclosure**PRODUCT FEATURES**

RACO liquidtight connectors are suitable for use in Class I, Div. 2, Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations  
 Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts  
 All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service  
 Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening  
 Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground  
 UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation  
 All steel/iron components are zinc electro plated for added corrosion protection  
 3/8 in. to 4 in. Malleable iron bodies  
 3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts  
 N/A

**UL LISTED**

Standard 514B, UL Listed E195969

**CSA**

C22.2 No. 18

**GENERAL PRODUCT INFORMATION**

Sub Class:	Insulated
Trade Size:	1/2 in.

**DRAWING DIMENSIONS**

Dimension A:	1-11/64 in.
Dimension B:	9/16 in.
Thread Spec. B:	1/2 in. - 14 NPT
Dimension C:	1-13/32 in.
Dimension D:	1-5/8 in.

**PACKAGING**

Package Type:	Carton
Std. Pkg.:	1
Ship Carton Qty.:	15
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	27.80
Ship Carton Length (in.):	6.13
Ship Carton Width (in.):	3.13
Ship Carton Height (in.):	6.13
Ctn Weight (Lbs.):	4.17
UPC Number:	050169354285
I2of5:	50050169354280