



## 90 DEGREE CONDUIT AND CORD CONNECTORS - DIE CAST ZINC

90 Degree Connectors Die Cast Zinc  
N/A

B49.1



Catalog #: 3545DC

### APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit  
Use to positively bond the conduit to a box or enclosure

### PRODUCT FEATURES

Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts  
All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service  
Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening  
Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground  
N/A

### CULUS

Conduit Fittings 3HNN

### GENERAL PRODUCT INFORMATION

Sub Class: Insulated  
Trade Size: 1-1/4 in.

### DRAWING DIMENSIONS

Dimension A: -  
Thread Spec. A: -  
Dimension B: -  
Thread Spec. B: -  
Dimension C: -  
Thread Spec. C: -  
Dimension C A/C: -  
Dimension C A/F: -  
Dimension D: -  
Thread Spec. D: -  
Dimension E: -  
Thread Spec. E: -  
Dimension F: -

### PACKAGING

Package Type: Carton  
Ship Carton Qty.: 10  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 67.50  
Ship Carton Length (in.): 8.07  
Ship Carton Width (in.): 6.10  
Ship Carton Height (in.): 6.10  
Ctn Weight (Lbs.): 6.75  
UPC Number: 050169980293  
I2of5: 50050169980298