




90 DEGREE GROUNDING CONDUIT AND CORD CONNECTORS

90° Insulated Connector with Ground Lug, Steel/Malleable Iron
N/A

B52



Catalog #: 3548-3

APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit, when installation of a copper or aluminum external bonding jumper is required RACO grounding liquidtight connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

- Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
- All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service
- Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
- Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
- All metallic components are zinc electro plated for added corrosion protection
- Malleable Iron castings mate with other components perfectly without strain or distortion
- 3/8 in. to 4 in. Malleable iron bodies
- 3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts

UL LISTED

Standard 514B, UL Listed E195969

cULus LISTED

GENERAL PRODUCT INFORMATION

Trade Size:	2 in.
Min. Grounding Wire Capacity:	#14 SOL.
Max Grounding Wire Capacity:	#4 STR.

DRAWING DIMENSIONS

Dimension A:	3-1/32 in.
Dimension B:	3/4 in.
Thread Spec. B:	2 in. - 11-1/2 NPT
Dimension C:	2-15/32 in.
Dimension D:	3 in.
Dimension E:	25/32 in.

PACKAGING

Package Type:	Carton
Ship Carton Qty.:	5
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	202.80
Ship Carton Length (in.):	8.81
Ship Carton Width (in.):	7.38
Ship Carton Height (in.):	6.56
Ctn Weight (Lbs.):	10.14
UPC Number:	050169354834
I2of5:	50050169354839