


**STRAIGHT STRAIN RELIEF CONDUIT AND CORD CONNECTORS****Straight Strain Relief Cord Connectors Steel/Malleable Iron
N/A****B57**

Catalog #: 3702-2

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
 RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

All steel/malleable construction provides mechanical strength
 Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
 Washers have cable size range imprinted for identification - eliminates misidentifying inventory
 Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
 All metallic components are zinc electro plated for added corrosion protection
 UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
 3/8 in. to 1 in. Steel bodies; 1-1/4 in. to 1-1/2 in. Malleable Iron bodies
 3/8 in. to 1 in. Steel nuts; 1-1/4 in. to 1-1/2 in. Malleable Iron nuts
 N/A

CULUS

UL File E195973

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.
 Cable Range: .250 - .375
 Form Size: 1

DRAWING DIMENSIONS

Dimension A: 1-1/16 in.
 Dimension B: 1/2 in.
 Thread Spec. B: 1/2 in. - 14 NPT
 Dimension C: 1-29/64 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 25
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 17.40
 Ship Carton Length (in.): 6.25
 Ship Carton Width (in.): 4.50
 Ship Carton Height (in.): 4.25
 Ctn Weight (Lbs.): 4.35
 UPC Number: 050169370223
 I2of5: 50050169370228