




STRAIGHT STRAIN RELIEF CONDUIT AND CORD CONNECTORS

Straight Strain Relief Cord Connectors Steel/Malleable Iron
N/A

B57



Catalog #: 3702-3

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have cable size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electro plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel bodies; 1-1/4 in. to 1-1/2 in. Malleable Iron bodies
- 3/8 in. to 1 in. Steel nuts; 1-1/4 in. to 1-1/2 in. Malleable Iron nuts
- N/A

CULUS

UL File E195973

GENERAL PRODUCT INFORMATION

Trade Size:	1/2 in.
Cable Range:	.375 - .425
Form Size:	1

DRAWING DIMENSIONS

Dimension A:	1-1/16 in.
Dimension B:	1/2 in.
Thread Spec. B:	1/2 in. - 14 NPT
Dimension C:	1-29/64 in.

PACKAGING

Package Type:	Carton
Ship Carton Qty.:	25
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	16.00
Ship Carton Length (in.):	6.25
Ship Carton Width (in.):	4.50
Ship Carton Height (in.):	4.25
Ctn Weight (Lbs.):	4.00
UPC Number:	050169370230
I2of5:	50050169370235