




STRAIGHT STRAIN RELIEF CONDUIT AND CORD CONNECTORS

Straight Strain Relief Cord Connectors Steel/Malleable Iron
N/A

B57



Catalog #: 3706-2

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have cable size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electro plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel bodies; 1-1/4 in. to 1-1/2 in. Malleable Iron bodies
- 3/8 in. to 1 in. Steel nuts; 1-1/4 in. to 1-1/2 in. Malleable Iron nuts
- N/A

CULUS

UL File E195973

GENERAL PRODUCT INFORMATION

Trade Size: 1-1/2 in.
 Cable Range: 1.250 - 1.400
 Form Size: 6

DRAWING DIMENSIONS

Dimension A: 2-13/32 in.
 Dimension B: 47/64 in.
 Thread Spec. B: 1-1/2 in. - 11-1/2 NPT
 Dimension C: 2-11/64 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 10
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 80.50
 Ship Carton Length (in.): 8.25
 Ship Carton Width (in.): 6.00
 Ship Carton Height (in.): 5.50
 Ctn Weight (Lbs.): 8.05
 UPC Number: 050169370629
 I2of5: 50050169370624