




90 DEGREE STRAIN RELIEF CONDUIT AND CORD CONNECTORS

90° Strain Relief Cord Connectors Steel/Malleable Iron
N/A

B58



Catalog #: 3792-4

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

- All steel/malleable construction provides mechanical strength
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
- Washers have cable size range imprinted for identification - eliminates misidentifying inventory
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- All metallic components are zinc electro plated for added corrosion protection
- Malleable iron bodies, Steel nuts
- N/A

CULUS

UL File E195973

GENERAL PRODUCT INFORMATION

Trade Size:	1/2 in.
Cable Range:	.425 - .500
Form Size:	1

DRAWING DIMENSIONS

Dimension A:	1-3/64 in.
Thread Spec. A:	1/2 in. - 14 NPT
Dimension B:	35/64 in.
Dimension C:	1-3/8 in.
Dimension D:	1-7/16 in.

PACKAGING

Package Type:	Carton
Ship Carton Qty.:	25
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	21.60
Ship Carton Length (in.):	8.25
Ship Carton Width (in.):	5.00
Ship Carton Height (in.):	4.00
Ctn Weight (Lbs.):	5.40
UPC Number:	050169379240
I2of5:	50050169379245