


**90 DEGREE STRAIN RELIEF CONDUIT AND CORD CONNECTORS****90° Strain Relief Cord Connectors Steel/Malleable Iron**  
N/A**B58**

Catalog #: 3792-6

**APPLICATIONS**

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable  
 RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

**PRODUCT FEATURES**

All steel/malleable construction provides mechanical strength  
 Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal  
 Washers have cable size range imprinted for identification - eliminates misidentifying inventory  
 Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel  
 All metallic components are zinc electro plated for added corrosion protection  
 Malleable iron bodies, Steel nuts  
 N/A

**CULUS**

UL File E195973

**GENERAL PRODUCT INFORMATION**

Trade Size: 1/2 in.  
 Cable Range: .500 - .600  
 Form Size: 2

**DRAWING DIMENSIONS**

Dimension A: 1-11/64 in.  
 Thread Spec. A: 1/2 in. - 14 NPT  
 Dimension B: 9/16 in.  
 Dimension C: 1-13/32 in.  
 Dimension D: 1-5/8 in.

**PACKAGING**

Package Type: Carton  
 Ship Carton Qty.: 25  
 Product UPC-A Labeled: No  
 Weight (Lbs. Per/C): 22.30  
 Ship Carton Length (in.): 8.25  
 Ship Carton Width (in.): 5.00  
 Ship Carton Height (in.): 4.00  
 Ctn Weight (Lbs.): 5.58  
 UPC Number: 050169379264  
 I2of5: 50050169379269