



Vertical Pin Standoff Bracket, 40" 28" Three-Phase

by CHANCE Utility
Catalog ID: 3SBM4028VV1

40" 28" Medium Duty Fiberglass Three-Phase Vertical Pin Standoff Bracket with 1" Plastisol Coated Threads



* Representative image

Product Details

General

Description - End Fitting	Vertical Pin
Material - Threads	1" Plastisol Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1350 lb
UPC	096359269878

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	40 in
Distance from Pole - Third Phase	28 in
Length	40.00 in
Mounting Bolt Spacing	8.00 in
Weight	19.4 lb

Logistics

Standard Package	5
------------------	---

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com