



0° 2-Position Cutout / Arrester Standoff Bracket (No Hardware), 48" 18" Three-Phase

by CHANCE Utility
Catalog ID: 3SBM4818CT

48" 18" Medium Duty Fiberglass 0° 2-Position Three-Phase Cutout / Arrester Standoff Bracket (No Hardware)



* Representative image

Product Details

General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359391388

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	18 in
Length	48.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6.00 in• 8.00 in
Weight	25.0 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Carton Quantity	5 EA
Standard Package	5

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com