



## SHALLOW SWITCH BOXES WITH NONMETALLIC SHEATHED CABLE CLAMPS

3-3/4 in. x 2 in. Switch Boxes, 1 in. Deep - Nongangable with Nonmetallic Sheathed Cable Clamps  
Q clamps, 1/4 in. Setback

A52



Catalog #: 404

### APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets  
RACO® Shallow switch boxes are made for use with furring strips and 1/4" paneling

### PRODUCT FEATURES

RACO® "D" bracket is pre-scored and can be broken off if needed  
Reference the Box Selection section in the front of this catalog for complete description of bracket types and features  
N/A

### COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at [www.ul.com](http://www.ul.com)

### FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

### GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable

### CONFIGURATION

End Knockouts: (1) 1/2 in.  
Ends Cable: 2  
Bracket Type: D, for Metal or Wood Studs  
Bracket Setback: 1/4 in.  
Side Knockout(s): ---  
Bottom Knockouts(s): ---

### PRODUCT MEASUREMENTS

Depth: 1 in.  
Cubic Inches (cm3): 6.5 (106.5)  
Wt. Ea. (Lbs.): 0.392  
Product Length (in.): 1.06  
Product Width (in.): 7.00  
Product Height (in.): 2.13

### PACKAGING

Minimum Pack Qty.: 25  
Std. Pkg.: 25  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 39.20  
Ship Carton Length (in.): 11.50  
Ship Carton Width (in.): 5.06  
Ship Carton Height (in.): 6.63  
Ctn Weight (Lbs.): 9.80  
Pallet Qty: 3600  
UPC Number: 050169004043  
I2of5: 40050169004041