



SHALLOW SWITCH BOXES WITH NONMETALLIC SHEATHED CABLE CLAMPS

3-3/4 in. x 2 in. Switch Boxes, 1 in. Deep - Nongangable with Nonmetallic Sheathed Cable Clamps
Q clamps, 1/4 in. Setback

A52



Catalog #: 404SP

APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets
RACO® Shallow switch boxes are made for use with furring strips and 1/4" paneling

PRODUCT FEATURES

RACO® "D" bracket is pre-scored and can be broken off if needed
Reference the Box Selection section in the front of this catalog for complete description of bracket types and features
N/A

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable

CONFIGURATION

End Knockouts: (1) 1/2 in.
Ends Cable: 2
Bracket Type: D, for Metal or Wood Studs
Bracket Setback: 1/4 in.
Side Knockout(s): ---
Bottom Knockouts(s): ---

PRODUCT MEASUREMENTS

Depth: 1 in.
Cubic Inches (cm³): 6.5 (106.5)
Wt. Ea. (Lbs.): 0.411
Product Length (in.): 1.06
Product Width (in.): 7.00
Product Height (in.): 2.13

PACKAGING

Minimum Pack Qty.: 6
Std. Pkg.: 6
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 41.10
Ship Carton Length (in.): 8.75
Ship Carton Width (in.): 4.00
Ship Carton Height (in.): 5.00
Ctn Weight (Lbs.): 2.47
Pallet Qty: 1824
UPC Number: 050169004043
I2of5: 50050169104045