

**SHALLOW SWITCH BOXES WITH NONMETALLIC SHEATHED CABLE CLAMPS****3-3/4 in. x 2 in. Switch Boxes, 1 in. Deep - Nongangable with Nonmetallic Sheathed Cable Clamps
Q clamps, 1/4 in. Setback****A52**

Catalog #: 405

APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets
 RACO® Shallow switch boxes are made for use with furring strips and 1/4" paneling

PRODUCT FEATURES

RACO® "D" bracket is pre-scored and can be broken off if needed
 Reference the Box Selection section in the front of this catalog for complete description of bracket types and features
 N/A

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable

CONFIGURATION

Ends Cable: 4
 Bracket Type: D, for Metal or Wood Studs
 Bracket Setback: 1/4 in.
 Side Knockout(s): ---
 Bottom Knockouts(s): ---

PRODUCT MEASUREMENTS

Depth: 1 in.
 Cubic Inches (cm3): 6.5 (106.5)
 Wt. Ea. (Lbs.): 0.392
 Product Length (in.): 1.06
 Product Width (in.): 7.00
 Product Height (in.): 2.13

PACKAGING

Minimum Pack Qty.: 25
 Std. Pkg.: 25
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 39.20
 Ship Carton Length (in.): 11.50
 Ship Carton Width (in.): 5.06
 Ship Carton Height (in.): 6.63
 Ctn Weight (Lbs.): 9.80
 Pallet Qty: 3600
 UPC Number: 050169004050
 I2of5: 50050169004055