



**SHALLOW SWITCH BOXES WITH NONMETALLIC SHEATHED CABLE CLAMPS**

**4 in. x 4 in. Switch Boxes, 1 in. Deep - Nongangable with Nonmetallic Sheathed Cable Clamps  
(2) Q clamps, 1/4 in. Setback**

**A52**



Catalog #: 418

**APPLICATIONS**

RACO® Switch boxes are used to house wiring devices such as switches and outlets  
RACO® Shallow switch boxes are made for use with furring strips and 1/4" paneling

**PRODUCT FEATURES**

RACO® "D" bracket is pre-scored and can be broken off if needed  
Reference the Box Selection section in the front of this catalog for complete description of bracket types and features  
418 will accept 4" square mudring or flat cover  
N/A

**UL LISTED**

File E195978

**COMPLIANCES**

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

**FIRE RESISTANCE**

Acceptable for use in 2-hour rated walls

**GENERAL PRODUCT INFORMATION**

Wiring System: Nonmetallic Sheathed Cable

**CONFIGURATION**

End Knockouts: (2) 1/2 in.  
Ends Cable: 4  
Bracket Type: D, for Metal or Wood Studs  
Bracket Setback: 1/4 in.  
Side Knockout(s): ---  
Bottom Knockouts(s): ---

**PRODUCT MEASUREMENTS**

Depth: 1 in.  
Cubic Inches (cm3): 14.8 (242.5)  
Wt. Ea. (Lbs.): 0.686  
Product Length (in.): 1.06  
Product Width (in.): 7.00  
Product Height (in.): 4.13

**PACKAGING**

Minimum Pack Qty.: 25  
Std. Pkg.: 25  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 68.60  
Ship Carton Length (in.): 11.25  
Ship Carton Width (in.): 8.50  
Ship Carton Height (in.): 8.50  
Ctn Weight (Lbs.): 17.15  
Pallet Qty: 2500  
UPC Number: 050169004180  
I2of5: 50050169004185