



\* Representative image

# Anchor, No Wrench, 4in x 54in Tripleye

by CHANCE Utility  
Catalog ID: 4345

No-Wrench 54" (1372 mm) long with 4" (101 mm) Helix Tripleye.

- No-Wrench Screw Anchors may be installed by hand or machine.
- Hot dipped galvanized per ASTM A153
- No-Wrench Screw Anchors can be installed to a greater depth to reach a firmer soil by using an extension rod

## Product Details

### General

Coating	Galvanized
Eye Nut Style	Tripleye
Number of Helices	1
Torque Rating	400 ft-lbs
Type	Helical Anchors
UPC	096359071990

### Dimensions

Anchor Helix Diameter(s)	4 in
Length	54.000 in
Rod Diameter	0.750 in
Weight	7.840 lb

### Logistics

Pallet Quantity	100 EA
Standard Package	1

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)