


**3 IN. X 2 IN. SWITCH BOXES - 1-1/2 TO 2-1/2 IN. DEEP WITH NONMETALLIC SHEATHED CABLE CLAMPS****2 in. Deep Switch Box - Gangable with Nonmetallic Sheathed Cable Clamps  
Plaster Ears****A50**

Catalog #: 445

**APPLICATIONS**

RACO® Switch boxes are used to house wiring devices such as switches and outlets  
N/A

**PRODUCT FEATURES**

Gangable switch boxes offer the option of constructing a box to hold two or more devices  
Plaster ears allow a box to be used in "old work" applications

**UL LISTED**

File E 195978

**COMPLIANCES**

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

**FIRE RESISTANCE**

Acceptable for use in 2-hour rated walls

**GENERAL PRODUCT INFORMATION**

Wiring System: Nonmetallic Sheathed Cable

**CONFIGURATION**

End Knockouts: ---  
Ends Cable: 4  
Bracket Type: No Bracket  
Side Knockout(s): ---  
Bottom Knockout(s): (1) 1/2 in.

**DRAWING DIMENSIONS**

Dimension A: 2 in.

**PRODUCT MEASUREMENTS**

Depth: 2 in.  
Cubic Inches (cm<sup>3</sup>): 10.3 (168.8)  
Wt. Ea. (Lbs.): 0.51  
Product Length (in.): 2.00  
Product Width (in.): 4.22  
Product Height (in.): 2.00

**PACKAGING**

Minimum Pack Qty.: 50  
Std. Pkg.: 50  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 51.30  
Ship Carton Length (in.): 11.38  
Ship Carton Width (in.): 8.25  
Ship Carton Height (in.): 10.63  
Ctn Weight (Lbs.): 25.65  
Pallet Qty: 4000  
UPC Number: 050169004456  
I2of5: 50050169004451