




**STRAIN RELIEF CONDUIT AND CORD CONNECTORS - NONMETALLIC**

**Straight Strain Relief Connectors Nylon**  
N/A

**B59**



Catalog #: 4703-2

**APPLICATIONS**

For use in dry or wet locations to provide a liquidtight and strain relief termination for flexible cord and cable  
RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

**PRODUCT FEATURES**

- Nylon construction is lightweight and easy to use
- Neoprene grommet
- Resists most common industrial corrosives
- Color-coded Gotcha® ring provides fast identification of cord size
- N/A

**UL LISTED**

Standard 514B

**CSA**

C22.2 No. 18

**GENERAL PRODUCT INFORMATION**

Trade Size:	3/4 in.
Cable Range:	.500 - .625
Color Code:	Brown
Form Size:	3

**DRAWING DIMENSIONS**

Dimension A:	1-31/64 in.
Dimension B:	35/64 in.
Dimension C:	1-5/8 in.
Dimension D:	49/64 in.

**PACKAGING**

Package Type:	Carton
Ship Carton Qty.:	15
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	11.20
Ship Carton Length (in.):	8.75
Ship Carton Width (in.):	5.00
Ship Carton Height (in.):	4.00
Ctn Weight (Lbs.):	1.68
UPC Number:	050169470329
I2of5:	50050169470324