




TYPE B CONDUIT AND CORD CONNECTORS - NONMETALLIC

Straight Connector, Type B - Nylon
N/A

B54



Catalog #: 4723

APPLICATIONS

For use in dry or wet locations when the conduit and fittings are not subject to physical damage
Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

PRODUCT FEATURES

All gray nonmetallic construction provides superior corrosion protection
Each connector is supplied with a Neoprene O-ring and nylon locknut
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
N/A

UL LISTED

Standard 514B

CSA

C22.2 No. 18

NEMA

NEMA Type 4x, 12 and 13

GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.

DRAWING DIMENSIONS

Dimension A: 1.53 in.
Dimension B: 2.22 in.
Dimension C: .58 in.
Dimension D: .74 in.
Dimension E: A/C 1.85 in., A/F 1.53 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 25
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 7.40
Ship Carton Length (in.): 10.00
Ship Carton Width (in.): 5.25
Ship Carton Height (in.): 4.31
Ctn Weight (Lbs.): 1.85
UPC Number: 050169947234
I2of5: 50050169047236