


## **TYPE B CONDUIT AND CORD CONNECTORS - NONMETALLIC**

Straight Connector, Type B - Nylon

B54





Catalog #: 4724-8

#### APPLICATIONS

For use in dry or wet locations when the conduit and fittings are not subject to physical damage Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

#### PRODUCT FEATURES

All gray nonmetallic construction provides superior corrosion protection

Each connector is supplied with a Neoprene O-ring and nylon locknut
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation N/A

### UL LISTED

Standard 514B

### CSA

C22.2 No. 18

## NEMA

NEMA Type 4x, 12 and 13

## GENERAL PRODUCT INFORMATION

Trade Size: 1 in.

# DRAWING DIMENSIONS

Dimension A: Dimension B: 1.80 in. 2.32 in. Dimension C: .72 in. Dimension D: .96 in.

A/C 1.94 in., A/F 1.80 in. Dimension E:

### PACKAGING

Carton Package Type: Std. Pkg.: Ship Carton Qty.: Product UPC-A Labeled: 10 Yes Weight (Lbs. Per/C): Ship Carton Length (in.): 8.00 8.75 Ship Carton Width (in.): 5.00 Ship Carton Height (in.): Ctn Weight (Lbs.): 4.00 0.80

050169472484 50050169472489 UPC Number: 12of5: