




TYPE B CONDUIT AND CORD CONNECTORS - NONMETALLIC

Straight Connector, Type B - Nylon
N/A

B54



Catalog #: 4724

APPLICATIONS

For use in dry or wet locations when the conduit and fittings are not subject to physical damage
Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

PRODUCT FEATURES

All gray nonmetallic construction provides superior corrosion protection
Each connector is supplied with a Neoprene O-ring and nylon locknut
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
N/A

UL LISTED

Standard 514B

CSA

C22.2 No. 18

NEMA

NEMA Type 4x, 12 and 13

GENERAL PRODUCT INFORMATION

Trade Size: 1 in.

DRAWING DIMENSIONS

Dimension A: 1.80 in.
Dimension B: 2.32 in.
Dimension C: .72 in.
Dimension D: .96 in.
Dimension E: A/C 1.94 in., A/F 1.80 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 10
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 8.00
Ship Carton Length (in.): 8.75
Ship Carton Width (in.): 5.00
Ship Carton Height (in.): 4.00
Ctn Weight (Lbs.): 0.80
UPC Number: 050169947241
I2of5: 50050169047243