


**SWIVEL-LOK TYPE B CONDUIT AND CORD CONNECTORS****Straight to 90° Type B Swivel Lok® Connector, Nylon  
N/A****B55**

Catalog #: 4732-8

**APPLICATIONS**

For use in dry or wet locations when the conduit and fittings are not subject to physical damage  
 Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

**PRODUCT FEATURES**

All gray nonmetallic construction provides superior corrosion protection  
 Each connector is supplied with a Neoprene O-ring and nylon locknut  
 UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation  
 SWIVEL-LOK® multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating the need to stock other angle connectors  
 N/A

**UL LISTED**

Standard 514B

**CSA**

C22.2 No. 18

**NEMA**

NEMA Type 4x, 12 and 13

**COMPLIANCES**

MSDS  
[www.hubbell-rtb.com/certifications/Hubbell-RACO MSDS for WP Boxes and Fittings, January 2015.pdf](http://www.hubbell-rtb.com/certifications/Hubbell-RACO MSDS for WP Boxes and Fittings, January 2015.pdf)

**GENERAL PRODUCT INFORMATION**

Trade Size: 1/2 in.

**DRAWING DIMENSIONS**

Dimension A: 3.27 in.  
 Dimension B: .57 in.  
 Dimension C: A/C 1.41 in., A/F 1.30 in.  
 Dimension D: 1.30 in.  
 Dimension E: 1.43 in.  
 Dimension F: 2.00 in.

**PACKAGING**

Package Type: Carton  
 Std. Pkg.: 1  
 Ship Carton Qty.: 20  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 9.30  
 Ship Carton Length (in.): 10.00  
 Ship Carton Width (in.): 5.25  
 Ship Carton Height (in.): 4.31  
 Ctn Weight (Lbs.): 1.85  
 UPC Number: 050169473283  
 I2of5: 50050169473288