




**EXTRA FLEXIBLE CONDUIT AND CORD CONNECTORS - NONMETALLIC**

**Straight Extra Flexible Tubing Connector, Nylon**  
N/A

**B56**



Catalog #: 4741

**APPLICATIONS**

For use in dry or wet locations when the conduit and fittings are not subject to physical damage  
Use extra flexible tubing and connectors whenever added flexibility is required for installation, operation, or maintenance

**PRODUCT FEATURES**

All black nonmetallic construction ends metal fatigue and separation problems, and provides superior corrosion resistance  
Each connector is supplied with a Neoprene O-ring and nylon locknut  
SWIVEL-LOK® multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating the need to stock other angle connectors  
N/A

**UL LISTED**

Standard 514B

**CSA**

C22.2 No. 18

**NEMA**

NEMA Type 4x, 12 and 13

**GENERAL PRODUCT INFORMATION**

Trade Size: 3/8 in.

**DRAWING DIMENSIONS**

Dimension A: 1.14 in.  
Dimension B: 1.63 in.  
Dimension C: .57 in.  
Dimension D: .42 in.  
Dimension E: A/C 1.41 in., A/F 1.30 in.

**PACKAGING**

Package Type: Carton  
Ship Carton Qty.: 25  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 1.20  
Ship Carton Length (in.): 8.75  
Ship Carton Width (in.): 5.00  
Ship Carton Height (in.): 4.00  
Ctn Weight (Lbs.): 0.30  
UPC Number: 050169047415  
I2of5: 50050169047410