




3 IN. X 2 IN. SWITCH BOXES - 1-1/2 TO 2-1/2 IN. DEEP WITH CONDUIT KO'S

2-1/2 in. Deep Switch Boxes - Gangable with Conduit KO's
No Plaster Ears

A47



Catalog #: 501

APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets
N/A

PRODUCT FEATURES

Gangable switch boxes offer the option of constructing a box to hold two or more devices

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

End Knockouts: (2) 1/2 in.
Ends Cable: ---
Bracket Type: No Bracket
Side Knockout(s): (4) 1/2 in.
Bottom Knockouts(s): (2) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2-1/2 in.

PRODUCT MEASUREMENTS

Depth: 2-1/2 in.
Cubic Inches (cm3): 12.5 (204.8)
Wt. Ea. (Lbs.): 0.529
Product Length (in.): 2.50
Product Width (in.): 3.38
Product Height (in.): 2.00

PACKAGING

Minimum Pack Qty.: 50
Std. Pkg.: 50
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 52.90
Ship Carton Length (in.): 13.50
Ship Carton Width (in.): 7.38
Ship Carton Height (in.): 11.25
Ctn Weight (Lbs.): 26.45
Pallet Qty: 3900
UPC Number: 050169905012
I2of5: 50050169905017